

ΜΙΥΙ

PROCESS VISCOMETER



TYPICAL APPLICATION FIELDS

- Chemical: polymers, plastics, resins, gels
- Printing and coating: inks, paints, lacquers, varnishes
- Food and beverage: milk, cheese, juices, sauces
- Refineries: diesel, gasoline, heavy fuel, bitumen,
- Pharmaceutics and cosmetics: gels capsules, shampoos

Whatever your industry, we understand and develop solutions for many applications. For a personalized approach, contact us at instruments@sofraser.com

THE PROVEN, 30-YEAR SENSOR IN PROCESS VISCOSITY MEASUREMENT

Sofraser's MIVI sensor is the expert viscometer on the market and is used in every process application and quality control condition. Reliable viscosity measurement in every fluid provides complete satisfaction to thousands of users worldwide. The versatile Sofraser MIVI sensor has many options making it the ideal industry instrument.

- Improved process operations: Reliable, repeatable and continuous measurements combined with superior quality result in permanent production efficiency and increased profitability.
- Both dynamic & kinematic viscosities available: With density measurement also available with the same sensor, kinematic viscosity can easily be calculated.
- One sensor, myriad choices: The MIVI sensor is used in standard and sanitary process conditions as well as harsh environments like dust, high temperature, high pressure and hazardous areas. Its measuring range easily adapts to different viscosities; up to 10mPa.s, it can provide high sensitivity capabilities at 0.01mPa.s. Multiple mounting options (inline, online, on reactor, measuring chamber) allow for flawless installation.
- Simple and long-lasting: The MIVI sensor guarantees a rapid return on investment because it is easy to install and is easy to use. With non-wearing parts, the MIVI requires almost no maintenance.
- **Matched with electronics:** The MIVI sensor matched with stateof-the-art display, data processing, and adjustable outputs capabilities electronic device, easily handles all process and quality control needs.

<u>Mountings:</u>







On reactor wall

On pipe angle

Measuring chamber

STANDARD FEATURES AND SPECIFICATIONS Any range from 0.1-10mPa.s to 1000-1000 000mPa.s Viscosity High sensitivity option : from 0.01 - 10mPa.s (more on measuring range request) Viscosity precision* ±0.2% of reading Viscosity ±0.5% of reading accuracy** Available ranges between 0.6g/cc to 1.6g/cc (only Density measuring with temperature probe option, 9701 electronics range and viscosity up to 500cP) ±0.005g/cc Density precision ±0.01g/cc Density accuracy** 0 to 200°C / 32 to 390°F Operating High temperature option up to 300°C / 570°F temperature Low temperature option down to -55°C / -67°F Up to 60bar / 870psi . Working pressure High pressure option up to 1400bar / 2000psi Stainless steel 316L Material Optional alloys: Hastelloy, 316Ti... Coating on PTFE, Amorphous Diamond-Like Carbon, Electropolish vibrating rod Sensor: 2.6kg / 5.7lb Weight Length: 238mm / 9 3/8" from sensor body to protection Size tube Flexible cable length: 3 meters / 118 inches Protection Water-tightness: IP67 / NEMA 6P ATEX Ex-proof agreement option ATEX Ex dIIC T1...T6 (gas) zone 1 • Ex proof ATEX Ex tD A21 IP67 T75°C ... T300°C (dust) agreement option FM Class I, Division 1, Groups A,B,C,D, T4A Japan (JIS), South Korea (KGS) • Regulatory CE marked (European conformity) Included temperature probe: thermowell inserted directly in the product (from -30°C / -20°F to 250°C / Options 480°F) Sanitary applications: 3A design

 Mounting flange (on reactor wall, on pipe angle)
Complete elbow mounting (inline) – Ø mini: 32mm /1 ¹/₄"
Measuring chamber - For small pipe diameter – Ø maxi : ¹/₂"
Other on request (immersion tube, etc.)

• * From 10% to 90% of the full scale range. Depends on electronic resolution

• ** From 10% to 90% of the full scale range. Depends on calibration options

MIVI PROCESS VISCOMETER

In 1981, Sofraser invented & patented the world's first vibrating viscometer at resonance frequency also called tuning-type.

The vibration amplitude varies according to the viscosity of the product in which the rod is immersed.

The active part of the sensor, a vibrating rod held in oscillation at resonance frequency, is driven by constant electrical power.

Sofraser remains unsurpassed regarding process reliability and accuracy.





